




Even Speedier Diagnosis of the Deterioration of Lead-acid Batteries

Measure and save data in as fast as 2 seconds, a 60% improvement from the legacy 3554 Easily create reports on your tablet or smartphone




Use Noise Reduction Technology

to Reliably Measure UPS Operation















Use the New Test Lead for the Back of Distribution Panels and Other Hard-to-reach Places

The innovative L-shape design makes it easier to connect the test lead to electrode terminals, decreasing time spent measuring batteries.





Test Leads to Fit your Application

PIN TYPE LEAD L2020





A: 70 mm (2.76 in) (Red), 150 mm (5.91 in) (Black, up to 630 mm (24.8 in)) B: 164 mm (6.46 in), L: 1941 mm (76.42 in) (Red)

PIN TYPE LEAD 9465-10 (Bundled accessory)



TIP PIN 9465-90

A: 45 mm (1.77 in) (Red), 105 mm (4.13 in) (Black, up to 515 mm (20.28 in)) B: 176 mm (6.93 in), L: 1883 mm (74.13 in)(Red)

(For the L2020, 9465-10)



PIN TYPE LEAD 9772

TIP PIN 9772-90 (For the 9772)



A: 45 mm (1.77 in) (Red), 105 mm (4.13 in) (Black, up to 515 mm (20.28 in))

B: 173 mm (6.81 in), L: 1880 mm (74.02 in)(Red)

REMOTE CONTROL



to hold or save the measurement.

Cable length: Approx. 2 m

CLIP TYPE LEAD WITH TEMPERATURE SENSOR 9460




A: 300 mm (11.81 in) B: 106 mm (4.17 in) L: 2268 mm (89.29 in)

LARGE CLIP TYPE LEAD 9467



A: 300 mm (11.81 in) B: 116 mm (4.57 in) L: 1360 mm (53.54 in) Large clip diameter: Approx. φ29 mm (1.14 in)

Regarding probe length



A: Between split to probe, B: Probe length, L: Total length

Quickly Save Data and Create Reports Right in the Field

Just connect the test lead to the terminal




Connect to the voltage terminal and measure



When the measured value stabilizes, save it automatically without having to operate the switch. Wait time can be as short as only 2 seconds to auto-save from when the test leads make contact with the battery terminals, cutting time by 60% compared to the legacy product.





Next measurement


Instantly submit loaded data


Create reports on-site

Data transfer

Dedicated application available

Not only can you view the data you loaded from the BT3554 into a tablet, smartphone, or PC in ledger format, you can also graph the data to display it by cubicle (up to 500 data sets). Then, instantly create reports on-site.







How to download the application:

Tablet or smartphone

Download it from the App Store® for iPhone® or iPad®, or download it from the Google Play™ Store for Android™ devices.

Just search for "GENNECT Cross".

• PC

Bundled CD-R, Download from our homepage.

The battery function in the App for the iPhone® and iPad® will be released in August 2016.

Interface specifications

USB	Transmission speed: USB 2.0, Connector: USB mini-B	
	Bluetooth® 4.0LE	
	Transmission distance: Approx. 10 m (32.81 ft), line-of-sight	
Supported OS: Android™ 4.3 or later, iOS 8 or later		
Bluetooth® (BT3554-01 only)	Supported Android™ devices: Devices that support Bluetooth* SMART or SMART READY Supported iOS devices: iPhone* 5 or later, third-generation iPad* or later, first-generation iPad mini™ or later, fifth-generation iPod Touch* or later	


- iPhone, iPad, iPad mini, and iPod Touch are registered trademarks of Apple Inc. in the United States and other countries.
- iOS is a trademark of Cisco in the United States and other countries.
- Bluetooth® is a registered trademark of Bluetooth SIG, Inc., and is used by HIOKI E.E. CORPORATION under license.
- $\mathsf{Android}^\mathsf{TM}$ and $\mathsf{Google}\,\mathsf{Play}^\mathsf{TM}$ are registered trademarks of Google, Inc

Trend display for past data*

Analyze in the office

Graphically display the trend of one cubical (max. 500 batteries) or the condition of selected batteries.

[Example of data displayed for selected batteries]



*Trend display is only available with a PC application.

Product Name: BATTERY TESTER BT3554

Model No. (Order code)	Wireless transmission
BT3554	_
BT3554-01	Built in Bluetooth® wireless technology

Accuracy specifications

Accuracy guaranteed for 1 year, Post-adjustment accuracy guaranteed for 1 year Temperature and humidity for guaranteed accuracy: 23°C ±5°C (73°F ±9°F), 80% RH or less, Warm-up time: None (Unnecessary), after zero-adjustment

Resistance measurement accuracy

Measurement current frequency: 1 kHz ±30 Hz, With function for avoiding noise frequency enabled: 1 kHz ±80 Hz

Measurement current accuracy: ±10%

Range	Max. display	Resolution	Measurement accuracy	Measurement Current
3 mΩ	3.100 mΩ	1 μΩ	±1.0% rdg. ±8 dgt.*	160 mA
30 mΩ	31.00 mΩ	10 μΩ		160 mA
300 mΩ	310.0 mΩ	100 μΩ	±0.8% rdg. ±6 dgt.	16 mA
3 Ω	3.100 Ω	1 mΩ		1.6 mA

^{*} If zero-adjustment was not performed, add the following values:

When model L2020 is used: ±5 dgt.

When model 9465-10 is used: $\pm 6 \text{ dgt}$.

When model 9772 is used: ±1 dgt.

When model 9460 is used: ±16 dgt

When model 9467 is used: ±5 dgt.

When using test leads that are not listed above, or test leads whose length has been extended, accuracy is guaranteed only after zero-adjustment is performed.

Voltage measurement accuracy

_			
Range	Max. display	Resolution	Measurement accuracy
6 V	±6.000 V	1 mV	.0000/ rda .6 dat
60 V	±60.00 V	10 mV	±0.08% rdg. ±6 dgt.

Temperature measurement accuracy

	,		
Measurement range	Max. display	Resolution	Measurement accuracy
-10 to 60°C	60°C	0.1°C	±1.0°C

Comparator function

Compares setting values (Resistance: 2 levels, Voltage: 1 level) and measured values Determination method: Following chart, beeping sound, red backlight lights up with beeping sound

Savable settings: 200 tables

Value for warning

	_	,	7
	Resistance	Resistance	Resistance
	(low)	(medium)	(high)
Voltage (high)	PASS	WARNING	FAIL
Voltage (low)	WARNING	WARNING	FAIL

General specifications

Measurement types		Internal resistance measurement for batteries (AC four-terminal method) Terminal voltage measurement for batteries (DC voltage) Temperature measurement (when using the 9460)		
Display upda	ate rate	Approx. 3 times/s		
Absolute ma: input voltage		±60 V DC max (No AC input allowed)		
Operating er	nvironment	Indoors, pollution degree 2, altitude up to 2000 m (6562 ft)		
Operating te		0°C to 40°C (32°F to 104°F), 80% RH or less (no condensation)		
Storage tem		-10°C to 50°C (14°F to 122°F), 80% RH or less (no condensation)		
Power supply	/	AA (LR6) Alkaline Batteries x 8		
Continuous o time	perating	Approx. 8.5 hours (When using alkaline batteries)		
Auto power sa	ave	Auto power off after 10 minutes unless during data transmission		
Dielectric str	rength	1.5 kV AC for 1 minute, between all measurement terminals and the USB terminal		
Applicable	Safety	EN 61010		
standards	EMC	EN 61326		
Dimensions		Approx. 192 mm (7.56 in) W x 121 mm (4.76 in) H x 55 mm (2.17 in) D		
Mass		Approx. 790 g (27.9 oz) (including batteries) BT3554 Approx. 800 g (28.2 oz) (including batteries) BT3554-01		
Accessories		PIN TYPE LEAD 9465-10, ZERO ADJUSTMENT BOARD, PC Software Application CD, Power-on option sticker, Neck strap, AA (LR6) alkaline batteries x 8, Fuse, USB cable, Carrying case, Instruction manual, Cautions for using radio waves (BT3554-01 only)		

Functions

HOLD	(1) Hold measured value by pressing the HOLD key or when shorting the EXT. HOLD terminal (2) Automatically hold measured value after it stabilizes
Memory storage	Saving, loading, and deleting measured values Saved items: Date, resistance, voltage, temperature, comparator threshold, judgment Storable data: 6000 sets (500 data sets per unit) Memory structure: 500 data sets per unit (12 units)
Auto-Memory function	Automatically saves measured values to memory when they are held
Memory loading	Load stored data on instrument or with PC application in order

*The thresholds for determining the pass/fail condition of a battery depend on the specifications and standards of the battery manufacturer, battery type, capacity, etc. It is important and necessary to always conduct battery testing against the internal resistance and terminal voltage of a new or reference battery.

In some cases, it may be difficult to determine the deterioration state of traditional open type (liquid) lead-acid or alkaline batteries, which demonstrate smaller changes in internal resistance than sealed lead acid batteries

The Advantages of 4-Terminal Measurement The Quality of Your Test Lead CAN Make a Difference


Value for warning Value for failure

-Explanation-

When measuring certain batteries such as lead-acid cells, the resulting measurement value may differ depending on the test leads used to conduct the measurement. This difference is due to the shape of the probe tip as well as the dimensions of the 4-terminal test leads used for measurement. However, despite a difference in value given by different test leads, it is safe to assume that each specific value reflects the correct value obtainable by the respective test leads.

Based on this principle, when diagnosing battery deterioration in a time series, it is particularly important to use test leads having the same tip shape and dimensions in order to maintain measurement consistency.

The difference in the measurement values obtained by different test leads is a physical phenomenon caused by the difference in distance between the SOURCE and SENSE pins of the test leads. This is more significant when the battery terminal contains a resistance higher than the internal resistance of the battery under test. The figure on the right demonstrates how even minute physical differences between the SOURCE and SENSE pins for two types of test leads can affect the detected voltage level of the battery.



Note: Company names and Product names appearing in this catalog are trademarks or registered trademarks of various companies

HIOKI E.E. CORPORATION

HEADQUARTERS

81 Koizumi, Ueda, Nagano, 386-1192, Japan TEL +81-268-28-0562 FAX +81-268-28-0568 http://www.hioki.com/ E-mail: os-com@hioki.co.jp

HIOKI (Shanghai) SALES & TRADING CO., LTD. TEL +86-21-63910090 FAX +86-21-63910360

http://www.hioki.cn / E-mail: info@hioki.com.cn

HIOKI SINGAPORE PTE. LTD. TEL +65-6634-7677 FAX +65-6634-7477 E-mail: info-sg@hioki.com.sg

HIOKI KOREA CO., LTD.

TEL +82-2-2183-8847 FAX +82-2-2183-3360 E-mail: info-kr@hioki.co.jp

HIOKI USA CORPORATION

TEL +1-609-409-9109 FAX +1-609-409-9108 http://www.hiokiusa.com / E-mail: hioki@hiokiusa.com